

Delphi Series V48SH, 1/16th Brick 50W DC/DC Power Modules: 48V in, 1.0V, 50Aout

The Delphi Series V48SH, 1/16th Brick, 48V input, single output, isolated DC/DC converter, is the latest offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc. This product family provides up to 100 watts of power in an industry standard 1/16th brick form factor (1.30" x 0.90"). The 1.0V output offers one of the highest output currents available and provides up to 84% efficiency at full load. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performance, as well as extremely high reliability under highly stressful operating conditions.For lower power needs, but in a similar small form factor, please check out Delta, V36SE (50W or 15A), S48SP (36W or 10A) and S36SE (17W or 5A) series standard DC/DC modules.

FEATURES

- High efficiency: 84% @ 1.0V/50A
- Size:

33.0x22.8x9.5mm (1.30"x0.90"x0.37") (W/O heat-spreader) 33.0x22.8x12.7mm (1.30"x0.90"x0.50") (With heat-spreader)

- Industry standard footprint and pinout
- Fixed frequency operation
- SMD and through-hole versions
- Input UVLO
- OTP and output OCP, OVP
- Output voltage trim: -20%, +10%
- Monotonic startup into normal and pre-biased loads
- 1500V isolation and basic insulation
- No minimum load required
- No negative current during power or enable on/off
- ISO 9001, TL 9000, ISO 14001, QS 9000, OHSAS18001 certified manufacturing facility
- IEC/EN/UL/CSA 62368-1, 2nd edition
- UL/cUL 60950-1 (US & Canada)

OPTIONS

- SMD pins
- Short pin lengths available
- Positive/Negative remote On/Off
- Open Frame/Heat spreader

APPLICATIONS

- Optical Transport
- Data Networking
- Communications
- Servers



TECHNICAL SPECIFICATIONS

(T_A=25°C, airflow rate=300 LFM, V_{in}=48Vdc, nominal Vout unless otherwise noted.)

PARAMETER	NOTES and CONDITIONS	V48SH1R050 (Standard)			
		Min.	Units		
ABSOLUTE MAXIMUM RATINGS					
Input Voltage Continuous		0		80	Vdc
Transient (100ms)	100ms	0		100	Vdc
Operating Ambient Temperature		-40		85	ç
Storage Temperature		-55		125	°C
Input/Output Isolation Voltage NPUT CHARACTERISTICS				1500	Vdc
Operating Input Voltage		36		75	Vdc
Input Under-Voltage Lockout					
Turn-On Voltage Threshold		32.5	34	35.5	Vdc
Turn-Off Voltage Threshold		30.5	32	33.5	Vdc
Lockout Hysteresis Voltage Maximum Input Current	100% Load, 36Vin	1	2	3 2.2	Vdc A
No-Load Input Current	100 % Loau, 30VIII		30	50	mA
Off Converter Input Current			10	15	mA
Inrush Current (I2t)	With 100uF external input capacitor			1	A ² s
Input Reflected-Ripple Current	P-P thru 12µH inductor, 5Hz to 20MHz			20	mA
Input Voltage Ripple Rejection	120 Hz		-60		dB
DUTPUT CHARACTERISTICS					
Output Voltage Set Point	Vin=48V, Io=Io.max, Tc=25°C	0.985	1.0	1.015	Vdc
Output Voltage Regulation Over Load	lo=lo, min to lo, max		±5		mV
Over Line	Vin=36V to 75V		±5		mV
Over Temperature	Tc=-40°C to 125°C		±10		mV
Total Output Voltage Range	Over sample load, line and temperature	0.97		1.03	V
Output Voltage Ripple and Noise	5Hz to 20MHz bandwidth			400	.,
Peak-to-Peak RMS	Full Load, 1µF ceramic, 10µF tantalum Full Load, 1µF ceramic, 10µF tantalum		80 20	120 50	m∨ mV
Operating Output Current Range	Full Load, The Ceramic, Tope tantalum	0	20	50	A
Output Over Current Protection	Output Voltage 10% Low	110		150	%
DYNAMIC CHARACTERISTICS					
Output Voltage Current Transient	48V, 10μF Tan & 1μF Ceramic load cap, 0.1A/μs				
Positive Step Change in Output Current Negative Step Change in Output Current	50% Io.max to 75% Io.max 75% Io.max to 50% Io.max		50 50		mV mV
Settling Time (within 1% Vout nominal)	75% IO.IIIax to 50% IO.IIIax		100		us
Turn-On Transient			.00		40
Start-Up Time, From On/Off Control		15		30	ms
Start-Up Time, From Input	0 500 0	15		28	ms
Maximum Output Capacitance	Cap ESR>=3mohm; Full load; 5% overshoot of Vout at startup;	0		10000	μF
EFFICIENCY					
100% Load	Vin=48V		84		%
60% Load SOLATION CHARACTERISTICS	Vin=48V		85		%
Input to Output				1500	Vdc
Isolation Resistance		10		.000	MΩ
Isolation Capacitance			1000		pF
FEATURE CHARACTERISTICS			050		kHz
Switching Frequency ON/OFF Control, Negative Remote On/Off logic			250		KIIZ
Logic Low (Module On)	Von/off	0		0.8	V
Logic High (Module Off)	Von/off	2.4		5	V
ON/OFF Control, Positive Remote On/Off logic					
Logic Low (Module Off)	Von/off	0		0.8	V
Logic High (Module On) Output Voltage Trim Range	Von/off Max rated current guaranteed at full trim range	2.4 -20		5 10	V %
	Max rated current guaranteed at full triminance Max rated current guaranteed at full remote	-20			
Output Voltage Remote Sense Range	sense range		450	10	%
Output Over-Voltage Protection GENERAL SPECIFICATIONS	Over full temp range; % of nominal Vout		150		%
MTBF	Per Telecordia SR-332 Issue 2, 80% load, 25°C,		4.3		M hours
	48Vin, 300LFM Without heat spreader				
Weight Weight	With heat spreader With heat spreader		13.3 21.5		grams grams
Over-Temperature Shutdown (Without heat spreader)	Refer to Figure 19 for Hot spot 1 location		129		°C
	(48Vin,80% Io, 200LFM,Airflow from Vin+ to Vo+) Refer to Figure 21 for Hot spot 2 location				
Over-Temperature Shutdown (With heat spreader)	(48Vin,80% Io, 200LFM,Airflow from Vin+ to Vo+)		122		°C
Over-Temperature Shutdown (NTC resistor)	Refer to Figure 19 for NTC resistor location		125		°C

ELECTRICAL CHARACTERISTICS CURVES




Figure 1: Efficiency vs. load current for minimum, nominal, and maximum input voltage at 25°C




Figure 2: Power dissipation vs. load current for minimum, nominal, and maximum input voltage at 25°C.




Figure 3: Typical full load input characteristics at room temperature

ELECTRICAL CHARACTERISTICS CURVES

For Negative Remote On/Off Start up




Figure 4: Turn-on transient at full rated load current (10 ms/div). Vin=48V. Top Trace: Vout, 0.5V/div; Bottom Trace: ON/OFF input, 5V/div




Figure 5: Turn-on transient at zero load current (10 ms/div). Vin=48V. Top Trace: Vout: 0.5V/div, Bottom Trace: ON/OFF input, 5V/div

For Input Voltage Start up




Figure 6: Turn-on transient at full rated load current (10 ms/div). Vin=48V. Top Trace: Vout, 0.5V/div; Bottom Trace: Vin, 20V/div




Figure 7: Turn-on transient at zero load current (10 ms/div). Vin=48V. Top Trace: Vout, 0.5V/div; Bottom Trace: Vin, 20V/div




Figure 8: Output voltage response to step-change in load current (75%-50%-75% of Io, max; di/dt = 0.1A/ μ s). Load cap: 10 μ F tantalum capacitor and 1 μ F ceramic capacitor. Top Trace: Vout (50mV/div, 500us/div), Bottom Trace: lout (10A/div). Scope measurement should be made using a BNC cable (length shorter than 20 inches). Position the load between 51 mm to 76 mm (2 inches to 3 inches) from the module

ELECTRICAL CHARACTERISTICS CURVES




Figure 9: Test set-up diagram showing measurement points for Input Terminal Ripple Current and Input Reflected Ripple Current.

Note: Measured input reflected-ripple current with a simulated source Inductance (LTEST) of 12 µH. Capacitor Cs offset possible battery impedance. Measure current as shown above




Figure 11: Input reflected ripple current, is, through a 12µH source inductor at nominal input voltage and rated load current (20 mA/div, 1us/div)




Figure 13: Output voltage ripple at nominal input voltage and rated load current (50 mV/div, 1us/div)

Load capacitance: 1µF ceramic capacitor and 10µF tantalum capacitor. Bandwidth: 20 MHz. Scope measurements should be made using a BNC cable (length shorter than 20 inches). Position the load between 51 mm to 76 mm (2 inches to 3 inches) from the module.




Figure 10: Input Terminal Ripple Current, i_c, at full rated output current and nominal input voltage with 12μH source impedance and 33μF electrolytic capacitor (200 mA/div, 1us/div)




Figure 12: Output voltage noise and ripple measurement test setup

DESIGN CONSIDERATIONS


Input Source Impedance

The impedance of the input source connecting to the DC/DC power modules will interact with the modules and affect the stability. A low ac-impedance input source is recommended. If the source inductance is more than a few μ H, we advise adding a 100 μ F electrolytic capacitor (ESR < 0.7 Ω at 100 kHz) mounted close to the input of the module to improve the stability.

Layout and EMC Considerations

Delta's DC/DC power modules are designed to operate in a wide variety of systems and applications. For design assistance with EMC compliance and related PWB layout issues, please contact Delta's technical support team. An external input filter module is available for easier EMC compliance design. Below is the reference design for an input filter tested with V48SH1R050 series to meet class B in CISSPR 22.

Schematic and Components List:



Cin is 100uF low ESR Aluminum cap:

CY is 1nF ceramic cap


CX is 3.3uF ceramic cap:

CY1 is 3.3nF ceramic cap:

CY2 is 3.3nF ceramic cap:

L1 is common-mode inductor ,L1=1mH:

Test Result:Vin=48V,lo=50A,



Blue Line is quasi peak mode; green line is average mode.

Safety Considerations

The power module must be installed in compliance with the spacing and separation requirements of the end-user's safety agency standard, i.e., IEC 62368-1: 2014 (2nd edition), EN 62368-1: 2014 (2nd edition), UL 62368-1, 2nd Edition, 2014-12-01 and CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12. IEC 60950-1: 2005, 2nd Edition + A1: 2009 + A2: 2013, EN 60950-1: 2006 + A11: 2009 + A1: 2010 + A12: 2011 + A2: 2013, UL 60950-1, 2nd Edition, 2011-10-14 and CSA C22.2 No. 60950-1-07, 2nd Edition, 2010-14, if the system in which the power module is to be used must meet safety agency requirements.

Basic insulation based on 75 Vdc input is provided between the input and output of the module for the purpose of applying insulation requirements when the input to this DC-to-DC converter is identified as TNV-2 or SELV. An additional evaluation is needed if the source is other than TNV-2 or SELV.

When the input source is SELV circuit, the power module meets SELV (safety extra-low voltage) requirements. If the input source is a hazardous voltage which is greater than 60 Vdc and less than or equal to 75 Vdc, for the module's output to meet SELV requirements, all of the following must be met:

- The input source must be insulated from the ac mains by reinforced or double insulation.
- The input terminals of the module are not operator accessible.
- A SELV reliability test is conducted on the system where the module is used, in combination with the module, to ensure that under a single fault, hazardous voltage does not appear at the module's output.

When installed into a Class II equipment (without grounding), spacing consideration should be given to the end-use installation, as the spacing between the module and mounting surface have not been evaluated. The power module has extra-low voltage (ELV) outputs when all inputs are ELV.

This power module is not internally fused. To achieve optimum safety and system protection, an input line fuse is highly recommended. The safety agencies require a Fast-acting fuse with 20A maximum rating to be installed in the ungrounded lead. A lower rated fuse can be used based on the maximum inrush transient energy and maximum input current.

Soldering and Cleaning Considerations

Post solder cleaning is usually the final board assembly process before the board or system undergoes electrical testing. Inadequate cleaning and/or drying may lower the reliability of a power module and severely affect the finished circuit board assembly test. Adequate cleaning and/or drying is especially important for un-encapsulated and/or open frame type power modules. For assistance on appropriate soldering and cleaning procedures, please contact Delta's technical support team.

FEATURES DESCRIPTIONS

Over-Current Protection

The modules include an internal output over-current protection circuit, which will endure current limiting for an unlimited duration during output overload. If the output current exceeds the OCP set point, the modules will automatically shut down, and enter hiccup mode or latch mode, the default is hiccup mode.

For hiccup mode, the module will try to restart after shutdown. If the over current condition still exists, the module will shut down again. This restart trial will continue until the over-current condition is corrected.

For latch mode, the module will latch off once it shutdown. The latch is reset by either cycling the input power or by toggling the on/off signal for one second.

Over-Voltage Protection

The modules include an internal output over-voltage protection circuit, which monitors the voltage on the output terminals. If this voltage exceeds the over-voltage set point, the module will shut down, and enter in hiccup mode or latch mode, The default is hiccup mode.

For hiccup mode, the module will try to restart after shutdown. If the over voltage condition still exists, the module will shut down again. This restart trial will continue until the over-voltage condition is corrected.

For latch mode, the module will latch off once it shutdown. The latch is reset by either cycling the input power or by toggling the on/off signal for one second.

Over-Temperature Protection

The over-temperature protection consists of circuitry that provides protection from thermal damage. If the temperature exceeds the over-temperature threshold the module will shut down, and enter in auto-restart mode or latch mode, the default is auto-restart mode.

For auto-restart mode, the module will monitor the module temperature after shutdown. Once the temperature is dropped and within the specification, the module will be auto-restart.

For latch mode, the module will latch off once it shutdown. The latch is reset by either cycling the input power or by toggling the on/off signal for one second.

Remote On/Off

The remote on/off feature on the module can be either negative or positive logic. Negative logic turns the module on during a logic low and off during a logic high. Positive logic turns the modules on during a logic high and off during a logic low.

Remote on/off can be controlled by an external switch between the on/off terminal and the Vi(-) terminal. The switch can be an open collector or open drain.

For negative logic if the remote on/off feature is not used, please short the on/off pin to Vi(-). For positive logic if the remote on/off feature is not used, please leave the on/off pin floating.




Figure 14: Remote on/off implementation

Remote Sense

Remote sense compensates for voltage drops on the output by sensing the actual output voltage at the point of load. The voltage between the remote sense pins and the output terminals must not exceed the output voltage sense range given here:

$$[Vo(+) - Vo(-)] - [SENSE(+) - SENSE(-)] \le 10\% \times Vout$$

This limit includes any increase in voltage due to remote sense compensation and output voltage set point adjustment (trim).




Figure 15: Effective circuit configuration for remote sense operation

If the remote sense feature is not used to regulate the output at the point of load, please connect SENSE(+) to Vo(+) and SENSE(-) to Vo(-) at the module.

The output voltage can be increased by both the remote sense and the trim; however, the maximum increase is the larger of either the remote sense or the trim, not the sum of both.

FEATURES DESCRIPTIONS (CON.)

When using remote sense and trim, the output voltage of the module is usually increased, which increases the power output of the module with the same output current.

Max rated current is guaranteed at full output voltage remote sense range.

Output Voltage Adjustment (TRIM)

To increase or decrease the output voltage set point, connect an external resistor between the TRIM pin and either the SENSE(+) or SENSE(-). The TRIM pin should be left open if this feature is not used.




Figure 16: Circuit configuration for trim-down (decrease output voltage)

If the external resistor is connected between the TRIM and SENSE (-) pins, the output voltage set point decreases (Fig. 18). The external resistor value required to obtain a percentage of output voltage change \triangle % is defined as:

$$Rtrim - down = \left[\frac{511}{\Delta} - 10.22\right](K\Omega)$$

Ex. When Trim-down -10% (1.0Vx0.9=0.9V)

$$Rtrim - down = \left[\frac{511}{10} - 10.22\right] (K\Omega) = 40.88 (K\Omega)$$




Figure 17: Circuit configuration for trim-up (increase output voltage)

If the external resistor is connected between the TRIM and SENSE (+) the output voltage set point increases (Fig. 19). The external resistor value required to obtain a percentage output voltage change \triangle % is defined as:

$$Rtrim - up = \frac{5.11 \text{Vo} (100 + \Delta)}{0.6 \Delta} - \frac{511}{\Delta} - 10.22 (K\Omega)$$

Ex. When Trim-up +10% (1.0V×1.1=1.1V)

$$Rtrim - up = \frac{5.11 \times 1.0 \times (100 + 10)}{0.6 \times 10} - \frac{511}{10} - 10.22 = 32.36 (K\Omega)$$

Trim resistor can also be connected to Vo+ or Vo- but it would introduce a small error voltage than the desired value.

The output voltage can be increased by both the remote sense and the trim, however the maximum increase is the larger of either the remote sense or the trim, not the sum of both.

When using remote sense and trim, the output voltage of the module is usually increased, which increases the power output of the module with the same output current.

Max rated current is guaranteed at full output voltage trim range.

THERMAL CONSIDERATIONS


Thermal management is an important part of the system design. To ensure proper, reliable operation, sufficient cooling of the power module is needed over the entire temperature range of the module. Convection cooling is usually the dominant mode of heat transfer.

Hence, the choice of equipment to characterize the thermal performance of the power module is a wind tunnel.

Thermal Testing Setup

Delta's DC/DC power modules are characterized in heated vertical wind tunnels that simulate the thermal environments encountered in most electronics equipment. This type of equipment commonly uses vertically mounted circuit cards in cabinet racks in which the power modules are mounted.

The following figure shows the wind tunnel characterization setup. The power module is mounted on a test PWB and is vertically positioned within the wind tunnel. The space between the neighboring PWB and the top of the power module is constantly kept at 6.35mm (0.25").



Note: Wind Tunnel Test Setup Figure Dimensions are in millimeters and (Inches)

Figure 18: Wind tunnel test setup

Thermal Derating

Heat can be removed by increasing airflow over the module. To enhance system reliability, the power module should always be operated below the maximum operating temperature. If the temperature exceeds the maximum module temperature, reliability of the unit may be affected.

THERMAL CURVES (WITHOUT HEAT SPREADER)




Figure 19: * Hot spot 1& NTC resistor temperature measured points




Figure 20: Output current vs. ambient temperature and air velocity @Vin=48V(Either Orientation, airflow from Vin+ to Vout+, without heat spreader)

THERMAL CURVES (WITH HEAT SPREADER)




Figure 21: * Hot spot 2 temperature measured point




Figure 22: Output current vs. ambient temperature and air velocity @Vin=48V(Either Orientation, airflow from Vin+ to Vout+, with heat spreader)


PICK AND PLACE LOCATION

33.0(1.30") PIN 1 16.10(0.634") Ø7.0 (0.28") MIN. AREA PICK AND PLACE LOCATION

NOTES:

ALL DIMENSIONS ARE IN MILLIMETERS AND (INCHES) TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.) X.XXmm±0.25mm(X.XXX in.±0.010 in.)

RECOMMENDED PAD LAYOUT (SMD)




RECOMENDED P.W.B. PAD LAYOUT


NOTES:

DIMENSIONS ARE IN MILLIMETERS AND (INCHES)
TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)
X.XXmm±0.25mm(X.XXX in.±0.010 in.)

SURFACE-MOUNT TAPE & REEL




LEADED (Sn/Pb) PROCESS RECOMMEND TEMP. PROFILE(for SMD models)



Note: The temperature refers to the pin of V48SH, measured on the pin +Vout joint.


LEAD FREE (SAC) PROCESS RECOMMEND TEMP. PROFILE(for SMD models)



Note: The temperature refers to the pin of V48SH, measured on the pin +Vout joint.

MECHANICAL DRAWING(WITH HEAT-SPREADER)

* For modules with through-hole pins and the optional heatspreader, they are intended for wave soldering assembly onto system boards; please do not subject such modules through reflow temperature profile.



NOTES:

DIMENSIONS ARE IN MILLIMETERS AND (INCHES)

TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)


X.XXmm±0.25mm(X.XXX in.±0.010 in.)

MECHANICAL DRAWING (WITHOUT HEAT-SPREADER)


Surface-mount module

33.0(1.30") 3.8(0.15") 11.43(0.450") 15.24(0.600"] .81(0.150" 7.62(0.300" 2.5(0.10") 27.94(1.100" +Vout 8 22.8(0.90") +SENSE 7 PZ ON/OFF TRIM 6 -SENSE 5¢ 6 3 − Vin -Vout 4


TOP VIEW



Through-hole module



TOP VIEW




NOTES:

Pin No.	<u>Name</u>	<u>Function</u>		
1	+Vin	Positive input voltage		
2	ON/OFF	Remote ON/OFF		
3	-Vin	Negative input voltage		
4	-Vout	Negative output voltage		
5	-Sense	Negative remote sense		
6	Trim	Output voltage trim		
7	+Sense	Positive remote sense		
8	+Vout	Positive output voltage		

Pin Specification:

All pins are copper alloy with matte-tin(Pb free) plated over Nickel under-plating.

RECOMMENDED PAD LAYOUT (FOR THROUGH-HOLE MODULE)



NOTES:

DIMENSIONS ARE IN MILLIMETERS AND (INCHES)

TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)

X.XXmm±0.25mm(X.XXX in.±0.010 in.)

PART NUMBERING SYSTEM

V	48	S	Н	1R0	50	N	R	F	Α
Type of Product	Input Voltage	Number of Outputs	Product Series	Output Voltage	Output Current	ON/OFF Logic	Pin Length/Type		Option Code
V - 1/16 Brick	48- 36V~75V	S - Single	H - High Power	1R0 - 1.0V	50 - 50A	N- Negative P- Positive	R - 0.170" N - 0.145" K - 0.110" M-SMD		A - Standard Functions H - with Heatspreader

MODEL LIST

MODEL NAME	INPUT		OUTPUT		EFF @ 100% LOAD	
V48SH1R050NNFA	36V~75V	2.2A	1.0V	50A	84%	

Default remote on/off logic is negative and pin length is 0.170"

For different remote on/off logic and pin length, please refer to part numbering system above or contact your local sales office. For modules with through-hole pins and the optional heatspreader, they are intended for wave soldering assembly onto system boards; please do not subject such modules through reflow temperature profile.

CONTACT: www.deltaww.com/dcdc E-MAIL: dcdc@deltaww.com

USA: Telephone:

East Coast: 978-656-3993 West Coast: 510-668-5100

Fax: (978) 656 3964

Europe:

Phone: +41 31 998 53 11 Fax: +41 31 998 53 53

Asia & the rest of world:

Telephone: +886 3 4526107 ext 6221~6226

Fax: +886 3 4513485

WARRANTY

Delta offers a two (2) year limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.