
Grand Delphi Series



Delphi DNM, Non-Isolated Point of Load DC/DC Power Modules: 2.8-5.5Vin, 0.75-3.63V/10A out

The Delphi Series DNM04, 2.8-5.5V input, single output, non-isolated Point of Load DC/DC converters are the latest offering from a world leader in power system and technology and manufacturing -- Delta Electronics, Inc. The DNM04 series provides a programmable output voltage from 0.75V to 3.63V using an external resistor. The DNM series has flexible and programmable tracking and sequencing features to enable a variety of startup voltages as well as sequencing and tracking between power modules. This product family is available in a surface mount or SIP package and provides up to 10A of current in an industry standard footprint. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performance and extremely high reliability under highly stressful operating conditions.

FEATURES

- High efficiency: 96% @ 5.0Vin, 3.3V/10A out
- Small size and low profile: (SIP)
 50.8x 13.4x 8.5 mm (2.00" x 0.53" x 0.33")
- Signle-in-line (SIP) packaging
- Standard footprint
- Voltage and resistor-based trim
- Pre-bias startup
- Output voltage tracking
- No minimum load required
- Output voltage programmable from 0.75Vdc to 3.63Vdc via external resistor
- Fixed frequency operation
- Input UVLO, output OTP, OCP
- Remote ON/OFF
- Remote sense
- ISO 9001, TL 9000, ISO 14001, QS9000, OHSAS18001 certified manufacturing facility
- UL/cUL 60950 (US & Canada) Recognized, and TUV (EN60950) Certified
- CE mark meets 73/23/EEC and 93/68/EEC directives

OPTIONS

- Negative On/Off logic
- Tracking feature
- SIP package

APPLICATIONS

- Telecom / DataCom
- Distributed power architectures
- Servers and workstations
- LAN / WAN applications
- Data processing applications





TECHNICAL SPECIFICATIONS

 $(T_A = 25^{\circ}C, airflow rate = 300 LFM, V_{in} = 2.8Vdc and 5.5Vdc, nominal Vout unless otherwise noted.)$

PARAMETER	NOTES and CONDITIONS	DNM04					
		Min.	Тур.	Max.	Max. Units		
ABSOLUTE MAXIMUM RATINGS							
nput Voltage (Continuous) Tracking Voltage		0		5.8 Vin,max	Vdc Vdc		
Operating Temperature		-40		85	°C		
Storage Temperature		-55		125	°C		
INPUT CHARACTERISTICS							
Operating Input Voltage	Vout \leq Vin –0.5	2.8		5.5	V		
Input Under-Voltage Lockout Turn-On Voltage Threshold			2.2		V		
Turn-Off Voltage Threshold			2.0		V		
Maximum Input Current	Vin=2.8V to 5.5V, lo=lo,max		2:0	10	A		
No-Load Input Current			70		mA		
Off Converter Input Current			5		mA		
Inrush Transient	Vin=2.8V to 5.5V, lo=lo,min to lo,max			0.1	A ² S		
Recommended Input Fuse OUTPUT CHARACTERISTICS				15	A		
Output Voltage Set Point	Vin=5V, Io=100% Io, max, Tc=25℃	-2.0	Vo,set	+2.0	% Vo,set		
Output Voltage Adjustable Range		0.7525		3.63	V		
Output Voltage Regulation							
Over Line	Vin=2.8V to 5.5V		0.3		% Vo,set		
Over Load	Io=Io,min to Io,max Tc=-40°C to 100°C		0.4		% Vo,set % Vo,set		
Over Temperature Total Output Voltage Range	Over sample load, line and temperature	-3.0	0.8	+3.0	% Vo,set		
Output Voltage Ripple and Noise	5Hz to 20MHz bandwidth	0.0		10.0	/3 00,301		
Peak-to-Peak	Full Load, 1µF ceramic, 10µF tantalum		25	50	mV		
RMS	Full Load, 1µF ceramic, 10µF tantalum		8	15	mV		
Output Current Range		0		10	Α		
Output Voltage Over-shoot at Start-up	Vout=3.3V		000	1	% Vo,set		
Output DC Current-Limit Inception Output Short-Circuit Current (Hiccup Mode)	lo.s/c		220 3.5		% Io Adc		
DYNAMIC CHARACTERISTICS	10,5/0		3.5		Auc		
Dynamic Load Response	10µF Tan & 1µF Ceramic load cap, 2.5A/µs						
Positive Step Change in Output Current	50% Io, max to 100% Io, max		200		mV		
Negative Step Change in Output Current	100% Io, max to 50% Io, max		200		mV		
Settling Time to 10% of Peak Deviation			25		μs		
Turn-On Transient Start-Up Time, From On/Off Control	Io=Io.max Vin=Vin,min, Vo=10% of Vo,set		4		ms		
Start-Up Time, From Input	Viii=Viii,Tiiii, Vo=10% of Vo,set		4		ms		
Output Voltage Rise Time	Time for Vo to rise from 10% to 90% of Vo,set		4	8	ms		
Maximum Output Startup Capacitive Load	Full load; ESR $\geq 1m\Omega$			1000	μF		
	Full load; ESR $\geq 10m\Omega$			5000	μF		
EFFICIENCY					0.1		
/o=3.3V	Vi=5V, 100% Load		96.0 94.2		%		
/o=2.5V /o=1.8V	Vi=5V, 100% Load Vi=5V, 100% Load		94.2		%		
Vo=1.5V	Vi=5V, 100% Load		91.4		%		
Vo=1.2V	Vi=5V, 100% Load		90.0		%		
Vo=0.75V	Vi=5V, 100% Load		86.3		%		
FEATURE CHARACTERISTICS							
Switching Frequency			300		kHz		
ON/OFF Control, (Negative logic) Logic Low Voltage	Module On, Von/off	-0.2		0.3	V		
Logic High Voltage	Module Off, Von/off	1.5		Vin,max	V		
Logic Low Current	Module On, Ion/off			10	μA		
Logic High Current	Module Off, Ion/off		0.2	1	mA		
ON/OFF Control, (Positive Logic)							
Logic High Voltage	Module On, Von/off			Vin,max	V		
Logic Low Voltage Logic Low Current	Module Off, Von/off Module On, Ion/off	-0.2	0.2	0.3 1	V mA		
Logic Low Current	Module Off, Ion/off		0.2	10	μΑ		
Fracking Slew Rate Capability		0.1		2	V/msec		
Tracking Delay Time	Delay from Vin.min to application of tracking voltage	10		_	ms		
Tracking Accuracy	Power-up 2V/mS		100	200	mV		
	Power-down 1V/mS		200	400	mV		
				0.1	V		
GENERAL SPECIFICATIONS MTBF	lo=80% of lo, max; Ta=25°C		21.91		M hours		
Wight			10		grams		
Over-Temperature Shutdown	Refer to Figure 45 for measuring point		130		°C		






Figure 1: Converter efficiency vs. output current (3.3V out)




Figure 3: Converter efficiency vs. output current (1.8V out)




Figure 5: Converter efficiency vs. output current (1.2V out)

DS_DNM04SIP10_07182012D




Figure 2: Converter efficiency vs. output current (2.5V out)




Figure 4: Converter efficiency vs. output current (1.5V out)




Figure 6: Converter efficiency vs. output current (0.75V out)

3






Figure 7: Output ripple & noise at 3.3Vin, 2.5V/10A out






Figure 9: Output ripple & noise at 5Vin, 3.3V/10A out










Figure 8: Output ripple & noise at 3.3Vin, 1.8V/10A out








Figure 12: Turn on delay time at 3.3Vin, 1.8V/10A out




Figure 13: Turn on delay time at 5Vin, 3.3V/10A out




Figure 15: Turn on delay time at remote turn on 5Vin, 3.3V/16A out




Figure 17: Turn on delay time at remote turn on with external capacitors (Co= $5000 \ \mu$ F) 5Vin, 3.3V/16A out




Figure 16: Turn on delay time at remote turn on 3.3Vin, 2.5V/16A




Figure 18: Turn on delay time at remote turn on with external capacitors (Co= $5000 \ \mu$ F) 3.3Vin, 2.5V/16A out

DS_DNM04SIP10_07182012D




Figure 19: Typical transient response to step load change at 2.5A/µS from 100% to 50% of lo, max at 5Vin, 3.3Vout (Cout = 1uF ceramic, 10µF tantalum)




Figure 21: Typical transient response to step load change at 2.5A/μS from 100% to 50% of Io, max at 5Vin, 1.8Vout (Cout =1uF ceramic, 10μF tantalum)




Figure 20: Typical transient response to step load change at 2.5A/μS from 50% to 100% of lo, max at 5Vin, 3.3Vout (Cout =1uF ceramic, 10μF tantalum)





Figure 22: Typical transient response to step load change at 2.5A/µS from 50% to 100% of lo, max at 5Vin, 1.8Vout (Cout = 1uF ceramic, 10µF tantalum)








Figure 24: Typical transient response to step load change at 2.5A/µS from 50% to 100% of Io, max at 3.3Vin, 2.5Vout (Cout =1uF ceramic, 10µF tantalum)




Figure 26: Typical transient response to step load change at 2.5A/ $\!\mu S$ from 50% to 100% of Io, max at 3.3Vin, 1.8Vout (Cout = 1uF ceramic, 10µF tantalum)




Figure 28: Turn on with Prebias 5Vin, 3.3V/0A out, Vbias = 1.0Vdc

2.5A/µS from 100% to 50% of Io, max at 3.3Vin,





Figure 27: Output short circuit current 5Vin, 0.75Vout




TEST CONFIGURATIONS




Note: Input reflected-ripple current is measured with a simulated source inductance. Current is measured at the input of the module.

Figure 29: Input reflected-ripple test setup



Note: Use a 10μ F tantalum and 1μ F capacitor. Scope measurement should be made using a BNC cable.

Figure 30: Peak-peak output noise and startup transient measurement test setup.



- Figure 31: Output voltage and efficiency measurement test setup
- Note: All measurements are taken at the module terminals. When the module is not soldered (via socket), place Kelvin connections at module terminals to avoid measurement errors due to contact resistance.

$$\eta = (\frac{Vo \times Io}{Vi \times Ii}) \times 100 \quad \%$$

DESIGN CONSIDERATIONS

Input Source Impedance

To maintain low noise and ripple at the input voltage, it is critical to use low ESR capacitors at the input to the module. Figure 32 shows the input ripple voltage (mVp-p) for various output models using 200 μ F(2 x100uF) low ESR tantalum capacitor (KEMET p/n: T491D107M016AS, AVX p/n: TAJD107M106R, or equivalent) in parallel with 47 μ F ceramic capacitor (TDK p/n:C5750X7R1C476M or equivalent). Figure 33 shows much lower input voltage ripple when input capacitance is increased to 400 μ F (4 x 100 μ F) tantalum capacitors in parallel with 94 μ F (2 x 47 μ F) ceramic capacitor.

The input capacitance should be able to handle an AC ripple current of at least:




Figure 32: Input voltage ripple for various output models, IO = 10 A (CIN = 2×100 μ F tantalum // 47 μ F ceramic)




Figure 33: Input voltage ripple for various output models, IO = 10 A (CIN = 4×100 µF tantalum // 2×47 µF ceramic)



DESIGN CONSIDERATIONS (CON.)

The power module should be connected to a low ac-impedance input source. Highly inductive source impedances can affect the stability of the module. An input capacitance must be placed close to the modules input pins to filter ripple current and ensure module stability in the presence of inductive traces that supply the input voltage to the module.

Safety Considerations

For safety-agency approval the power module must be installed in compliance with the spacing and separation requirements of the end-use safety agency standards.

For the converter output to be considered meeting the requirements of safety extra-low voltage (SELV), the input must meet SELV requirements. The power module has extra-low voltage (ELV) outputs when all inputs are ELV.

The input to these units is to be provided with a maximum 15A time-delay fuse in the ungrounded lead.

FEATURES DESCRIPTIONS

Remote On/Off

The DNM/DNL series power modules have an On/Off pin for remote On/Off operation. Both positive and negative On/Off logic options are available in the DNM/DNL series power modules.

For positive logic module, connect an open collector (NPN) transistor or open drain (N channel) MOSFET between the On/Off pin and the GND pin (see figure 34). Positive logic On/Off signal turns the module ON during the logic high and turns the module OFF during the logic low. When the positive On/Off function is not used, leave the pin floating or tie to Vin (module will be On).

For negative logic module, the On/Off pin is pulled high with an external pull-up $5k\Omega$ resistor (see figure 35). Negative logic On/Off signal turns the module OFF during logic high and turns the module ON during logic low. If the negative On/Off function is not used, leave the pin floating or tie to GND. (module will be On)




Figure 34: Positive remote On/Off implementation




Figure 35: Negative remote On/Off implementation

Over-Current Protection

To provide protection in an output over load fault condition, the unit is equipped with internal over-current protection. When the over-current protection is triggered, the unit enters hiccup mode. The units operate normally once the fault condition is removed.



FEATURES DESCRIPTIONS (CON.)

Over-Temperature Protection

The over-temperature protection consists of circuitry that provides protection from thermal damage. If the temperature exceeds the over-temperature threshold the module will shut down. The module will try to restart after shutdown. If the over-temperature condition still exists during restart, the module will shut down again. This restart trial will continue until the temperature is within specification

Remote Sense

The DNM/DNL provide Vo remote sensing to achieve proper regulation at the load points and reduce effects of distribution losses on output line. In the event of an open remote sense line, the module shall maintain local sense regulation through an internal resistor. The module shall correct for a total of 0.5V of loss. The remote sense line impedance shall be < 10Ω .




Figure 36: Effective circuit configuration for remote sense operation

Output Voltage Programming

The output voltage of the DNM/DNL can be programmed to any voltage between 0.75Vdc and 3.63Vdc by connecting one resistor (shown as Rtrim in Figure 37) between the TRIM and GND pins of the module. Without this external resistor, the output voltage of the module is 0.7525 Vdc. To calculate the value of the resistor Rtrim for a particular output voltage Vo, please use the following equation:

$$Rtrim = \left[\frac{21070}{Vo - 0.7525} - 5110\right]\Omega$$

For example, to program the output voltage of the DNL module to 1.8Vdc, Rtrim is calculated as follows:

$$Rtrim = \left[\frac{21070}{1.8 - 0.7525} - 5110\right]\Omega = 15K\Omega$$

DNL can also be programmed by apply a voltage between the TRIM and GND pins (Figure 38). The following equation can be used to determine the value of Vtrim needed for a desired output voltage Vo:

DS_DNM04SIP10_07182012D

 $Vtrim = 0.7 - 0.1698 \times (Vo - 0.7525)$

For example, to program the output voltage of a DNL module to 3.3 Vdc, Vtrim is calculated as follows

$$Vtrim = 0.7 - 0.1698 \times (3.3 - 0.7525) = 0.267V$$




Figure 37: Circuit configuration for programming output voltage using an external resistor




Figure 38: Circuit Configuration for programming output voltage using external voltage source

Table 1 provides Rtrim values required for some common output voltages, while Table 2 provides value of external voltage source, Vtrim, for the same common output voltages. By using a 1% tolerance trim resistor, set point tolerance of $\pm 2\%$ can be achieved as specified in the electrical specification.

Table	1
-------	---

Vo(V)	Rtrim(KΩ)
0.7525	Open
1.2	41.97
1.5	23.08
1.8	15.00
2.5	6.95
3.3	3.16
3.63	2.21

Table 2

Vo(V)	Vtrim(V)
0.7525	Open
1.2	0.624
1.5	0.573
1.8	0.522
2.5	0.403
3.3	0.267
3.63	0.211



FEATURE DESCRIPTIONS (CON.)

The amount of power delivered by the module is the voltage at the output terminals multiplied by the output current. When using the trim feature, the output voltage of the module can be increased, which at the same output current would increase the power output of the module. Care should be taken to ensure that the maximum output power of the module must not exceed the maximum rated power (Vo.set x lo.max \leq P max).

Voltage Margining

Output voltage margining can be implemented in the DNL modules by connecting a resistor, R margin-up, from the Trim pin to the ground pin for margining-up the output voltage and by connecting a resistor, R margin-down, from the Trim pin to the output pin for margining-down. Figure 39 shows the circuit configuration for output voltage margining. If unused, leave the trim pin unconnected. A calculation tool is available from the evaluation procedure which computes the values of R margin-up and R margin-down for a specific output voltage and margin percentage.





Figure 39: Circuit configuration for output voltage margining

Voltage Tracking

The DNM family was designed for applications that have output voltage tracking requirements during power-up and power-down. The devices have a TRACK pin to implement three types of tracking method: sequential start-up, simultaneous and ratio-metric. TRACK simplifies the task of supply voltage tracking in a power system by enabling modules to track each other, or any external voltage, during power-up and power-down.

By connecting multiple modules together, customers can get multiple modules to track their output voltages to the voltage applied on the TRACK pin. The output voltage tracking feature (Figure 40 to Figure 42) is achieved according to the different external connections. If the tracking feature is not used, the TRACK pin of the module can be left unconnected or tied to Vin.

For proper voltage tracking, input voltage of the tracking power module must be applied in advance, and the remote on/off pin has to be in turn-on status. (Negative logic: Tied to GND or unconnected. Positive logic: Tied to Vin or unconnected)







Figure 40: Sequential






Figure 41: Simultaneous







Figure 42: Ratio-metric

FEATURE DESCRIPTIONS (CON.)

Sequential Start-up


Sequential start-up (Figure 40) is implemented by placing an On/Off control circuit between Vo_{PS1} and the On/Off pin of PS2.



Simultaneous

Simultaneous tracking (Figure 41) is implemented by using the TRACK pin. The objective is to minimize the voltage difference between the power supply outputs during power up and down.

The simultaneous tracking can be accomplished by connecting Vo_{PS1} to the TRACK pin of PS2. Please note the voltage apply to TRACK pin needs to always higher than the Vo_{PS2} set point voltage.



Ratio-Metric


Ratio-metric (Figure 42) is implemented by placing the voltage divider on the TRACK pin that comprises R1 and R2, to create a proportional voltage with Vo_{PS1} to the Track pin of PS2.

For Ratio-Metric applications that need the outputs of PS1 and PS2 reach the regulation set point at the same time.

The following equation can be used to calculate the value of R1 and R2.

The suggested value of R2 is $10k\Omega$.

$$\frac{V_{O,PS2}}{V_{O,PS1}} = \frac{R_2}{R_1 + R_2}$$





THERMAL CONSIDERATIONS

Thermal management is an important part of the system design. To ensure proper, reliable operation, sufficient cooling of the power module is needed over the entire temperature range of the module. Convection cooling is usually the dominant mode of heat transfer.

Hence, the choice of equipment to characterize the thermal performance of the power module is a wind tunnel.


Thermal Testing Setup

Delta's DC/DC power modules are characterized in heated vertical wind tunnels that simulate the thermal environments encountered in most electronics equipment. This type of equipment commonly uses vertically mounted circuit cards in cabinet racks in which the power modules are mounted.

The following figure shows the wind tunnel characterization setup. The power module is mounted on a test PWB and is vertically positioned within the wind tunnel. The height of this fan duct is constantly kept at 25.4mm (1").

Thermal Derating

Heat can be removed by increasing airflow over the module. To enhance system reliability, the power module should always be operated below the maximum operating temperature. If the temperature exceeds the maximum module temperature, reliability of the unit may be affected.



Note: Wind Tunnel Test Setup Figure Dimensions are in millimeters and (Inches)

Figure 43: Wind tunnel test setup






Figure 44: Temperature measurement location * The allowed maximum hot spot temperature is defined at 125 ${\rm \mathcal{C}}$




Figure 45: DNM04S0A0R10 (Standard) Output current vs. ambient temperature and air velocity @Vin=5V, Vo=3.3V(Either Orientation)




Figure 46: DNM04S0A0R10(Standard) Output current vs. ambient temperature and air velocity @Vin=5V, Vo=0.75V(Either Orientation)

Figure 47: DNM04S0A0R10 (Standard) Output current vs. ambient temperature and air velocity @Vin=3.3V, Vo=2.5V(Either Orientation)





Figure 48: DNM04S0A0R10 (Standard) Output current vs. ambient temperature and air velocity @ Vin=3.3V, Vo=0.75V(Either Orientation)



MECHANICAL DRAWING

SMD PACKAGE (OPTIONAL)

SIP PACKAGE



NOTES: DIMENSIONS ARE IN MILLIMETERS AND (INCHES) TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.) X.XXmm±0.25mm(X.XXX in.±0.010 in.)



PART NUMBERING SYSTEM

DNM	04	S	0A0	R	10	Р	F	D
Product Series	Input Voltage	Numbers of Outputs	Output Voltage	Package Type	Output Current	On/Off logic		Option Code
DNL - 16A	04 - 2.8~5.5V	S - Single	0A0 -	R - SIP	10 - 10A	N- negative	F- RoHS 6/6	D - Standard Function
DNM - 10A	10 - 8.3~14V		Programmable	S - SMD		P- positive	(Lead Free)	
DNS - 6A								

MODEL LIST

Model Name	Packaging	Input Voltage	Output Voltage	Output Current	Efficiency 5.0Vin, 100% load
DNM04S0A0R10PFD	SIP	2.8 ~ 5.5Vdc	0.75 V~ 3.63Vdc	10A	96.0% (3.3V)
DNM04S0A0R10NFD	SIP	2.8 ~ 5.5Vdc	0.75 V~ 3.63Vdc	10A	96.0% (3.3V)
DNM04S0A0S10PFD	SMD	2.8 ~ 5.5Vdc	0.75 V~ 3.63Vdc	10A	96.0% (3.3V)
DNM04S0A0S10NFD	SMD	2.8 ~ 5.5Vdc	0.75 V~ 3.63Vdc	10A	96.0% (3.3V)

CONTACT: www.deltaww.com/dcdc

USA:
Telephone:
East Coast: 978-656-3993
West Coast: 510-668-5100
Fax: (978) 656 3964
Email: DCDC@delta-corp.com

Europe: Phone: +31-20-655-0967 Fax: +31-20-655-0999 Email: <u>DCDC@delta-es.com</u> Asia & the rest of world: Telephone: +886 3 4526107 ext 6220-6224 Fax: +886 3 4513485 Email: DCDC@delta.com.tw

WARRANTY

Delta offers a two (2) year limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.